

PROLINE 100™ Series HE

Multi-Bag Filter Housing for High Volume Applications



PROLINE 100™ Series HE
with 4 bag capacity

*The most competitively priced
multi-bag vessel Eaton has to offer*

- 100 PSI, non-code vessel, for a wide variety of filtration applications.
- 304 stainless steel for high corrosion resistance.
- Unique 3-point bag hold down bayonet fittings ensure high quality of seal between each filter bag and housing body.
- A spring assisted lifting mechanism balances the cover perfectly—giving it a weightless feel.
- Positive O-ring sealing offers easy and safe operation.
- Side inlet and tangential outlet to reduce housing height and provide easy and full drainage.



Standard sizes

No. of Bags	Connection Size	Filter Bag Size
4	4"	02
6	6"	02
8	6"	02
12	8"	02

EATON

Powering Business Worldwide

Specifications

- Use with standard #2 size filter bags.
- 304 stainless steel construction with bead blast external finish.
- 150# RF flanged inlet and outlet ports for side in/tangential out configuration.
- Units come standard with a stainless steel support basket.
- Heavy-duty stainless steel mounting legs are included.
- Buna-N O-rings for the cover are standard. Viton or EPDM are optional.
- Available as inline configuration or loop piping configuration (shown).



PROLINE 100™ Series HE
with 8 bag capacity



RELATED PRODUCT

PROLINE 100™ Series SE offers the revolutionary QIC-LOCK™ opening mechanism for fast and easy access to the filter chamber. Available in 4, 6, 8 and 12 bag configurations.

Filter Bags



PROGAF™
Absolute rated
with up to 15
layers of media

ACCUGAF™
Absolute rated
at 99%

LOFCLEAR™
Oil removal
and gels

HAYFLOW™
Up to 5 times the
life of standard
bags

DURAGAF™
Up to 3 times the
life of standard
bags

SENTINEL®
High quality,
durable
performance

UNIBAG™
Efficiency with
an economical
advantage

North America – HQ
70 Wood Avenue, South
2nd Floor
Iselin, NJ 08830
Toll Free: (800) 656-3344
(North America only)
Voice: (732) 767-4200
Fax: (952) 906-3706

Brazil
Av. Julia Gaioli, 474 –
Bonsucesso
07251-500 – Guarulhos
Brazil
Voice: +55 (11) 2465-8822
Fax: +55 (11) 2465-8884

Singapore
4 Loyang Lane #04-01/02
Singapore 508914
Voice: +65-6825-1668
Fax: +65-6825-1639

*For more information,
please e-mail us at
filtrationinfo@eaton.com
or call 732-767-4200.*

*Visit us online at
filtration.eaton.com for
a complete list of Eaton's
filtration products.*

©2011 Eaton Corporation. All Rights Reserved.
All trademarks and registered trademarks are the
property of their respective owners. Litho USA

Europe/Africa/Middle East
Auf der Heide 2
53947 Nettersheim
Germany
Voice: +49-2486-809-0
Fax: +49-2486-809-800

China
No.3, Lane 280, Linhong Road
Changning District, 200335
Shanghai, P.R. China
Voice: +86-21-5200-0099
Fax: +86-21-5200-0400

All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.